| <u>├──</u> ──     |  |
|-------------------|--|
|                   | OSAGE AMBULANCE  |
|                   | 2024 WARRIOR   |
|                   | ORDER FORM   |
|                   | LAST UPDATED 05/16/2022                                  |
|                   |  |
| Dealer Name:      | Southeatern Specialty Vehicles                           |
| Salesperson:      | Dennis Tingen  |
| Customer Name:    | North Carolina Sheriff's Association Purchasing Contract |
| & Address         |  |
|                   |  |
|                   |  |
|                   |  |
|                   |  |
| Shipping Address: |  |
|                   |  |
|                   |  |
|                   |  |
|                   |  |
|                   |  |
| Fleet Number:     |  |
|                   |  |
| Contact Name:     |  |
| Email:            |  |
| Phone:            |  |
|                   |  |
| <i>Fax:</i>       |  |
| Chassis Type:     | Manadas Carintas   |
|                   | Mercedes Sprinter  |
| Osage Unit #:     |  |
|                   |  |
| VIN:              |  |
|                   |  |
|                   |  |
|                   |  |
|                   |  |
|                   |  |

| Qty     | CHEVROLET  | G-SERIES TYPE III - 2024 CHASSIS ONLY     |  |
|---------|--|---|--|
|         |  |   |  |
|         | Chevy G3500, 139" WB - Gas                             | EST                                       |  |
|         | Chevy G4500, 159" WB - Gas                             | EST                                       |  |
|         |  |   |  |
|         | CHEVROLET G  | -SERIES TYPE III - 2024 CONVERSION ONLY   |  |
|         | Character 2149 Wearing                                 |   |  |
|         | Chevrolet 2148 Warrior<br>Chevrolet 2168 Super Warrior |   |  |
|         | Chevrolet 2108 Super Warnon                            |   |  |
|         | FORD F-9   | SERIES TYPE III - 2024 CHASSIS ONLY       |  |
|         |  |   |  |
|         | Ford E350, 138" WB - GAS                               | EST                                       |  |
|         | Ford E450, 158" WB - GAS                               | EST                                       |  |
|         |  |   |  |
|         | FORD E-SEI   | RIES TYPE III - 2024 CONVERSION ONLY      |  |
|         |  |   |  |
|         | Ford 2148 Warrior                                      |   |  |
|         | Ford 2168 Super Warrior                                |   |  |
|         |  |   |  |
|         | MERCEDES   | S-BENZ SPRINTER - 2024 CHASSIS ONLY       |  |
|         |  |   |  |
| 1       | Mercedes-Benz Sprinter Diesel Chassis                  | EST                                       |  |
|         | MEDGEDEG D   |   |  |
|         | MERCEDES-B   | ENZ SPRINTER - 2024 CONVERSION ONLY       |  |
| 1       | Mercedes-Benz Sprinter 2148 Warrior III                |   |  |
| <u></u> |  |   |  |
|         | FORD F-SERIES  | ГҮРЕ I - 2024 w/UREA - D.E.F CHASSIS ONLY |  |
|         |  | (Call for Chassis Availability)           |  |
|         | F-450, 169" WB, 4x2                                    | EST                                       |  |
|         | F-450, 169" WB, 4x4                                    | EST                                       |  |
|         | F-550, 193" WB, 4x2                                    | EST                                       |  |
|         | F-550, 193" WB, 4x4                                    | EST                                       |  |
|         | Option: Liquid Spring Suspension (Front: 11            | 10lbs, Rear: 150lbs)                      |  |
|         | Option: Add Front Liquid Spring                        |   |  |
|         | Option: Add Aluminum Wheels                            |   |  |
|         |  |   |  |
|         | FORD F-SEI   | RIES TYPE I - 2024 GAS - CHASSIS ONLY     |  |
|         | F-450, 169" WB, 4x2                                    | (Call for Chassis Availability)<br>EST    |  |
|         | F-450, 169 WB, 4x2<br>F-450, 169" WB, 4x4              | EST                                       |  |
|         | F-550, 193" WB, 4x2                                    | EST                                       |  |
|         | F-550, 193" WB, 4x4                                    | EST                                       |  |
|         | Option: Liquid Spring Suspension (Front: 110lt         |   |  |
|         | Option: Add Front Liquid Spring                        |   |  |
|         | Option: Add Aluminum Wheels                            |   |  |
|         |  |   |  |
|         | FORD F-SE  | CRIES TYPE I - 2024 CONVERSION ONLY       |  |
|         |  |   |  |
|         | Ford 2148 Warrior                                      |   |  |
|         | Ford 2168 Super Warrior                                |   |  |

| _ | RAM TYPE I w/UREA - 2024   | CHASSIS ONLY       |
|---|--|--------------------|
|   | Ram 4500, 168" WB, 4x2   | EST                |
|   | Ram 4500, 168" WB, 4x2   | EST                |
|   | Ram 5500, 192" WB, 4x2   | EST                |
|   | Ram 5500, 192" WB, 4x2   | EST                |
|   | Option: Liquid Spring Suspension   | EST                |
|   | Option: Add Front Liquid Spring  |                    |
|   | Option: Add Aluminum Wheels  |                    |
|   | Option: Add Aluminum wheels  |                    |
| — |  |                    |
| _ | RAM TYPE I - 2024 GAS - C  | HASSIS UNLY        |
|   |  | 700                |
|   | Ram 4500, 168" WB, 4x2   | EST                |
|   | Ram 4500, 168" WB, 4x4   | EST                |
|   | Ram 5500, 192" WB, 4x2   | EST                |
|   | Ram 5500, 192" WB, 4x4   | EST                |
|   | Option: Liquid Spring Suspension   |                    |
|   | Option: Add Front Liquid Spring  |                    |
|   | Option: Add Aluminum Wheels  |                    |
|   |  |                    |
| _ | RAM TYPE I 2024 CONVE  | RSION ONLY         |
|   |  |                    |
|   | Ram 2148 Warrior   |                    |
|   | Ram 2168 Super Warrior   |                    |
|   |  |                    |
|   | CHEVROLET TYPE I - 2024  | CHASSIS ONLY       |
|   | Chevy 5500, 189" WB, 4x2 w/Liquid Spring (Includes TM-21 A/C Con   | mprossor) EST      |
| _ | Chevy 5500, 189° WB, 4x2 w/Liquid Spring (Includes TM-21 A/C Con<br>Chevy 5500, 189° WB, 4x4 w/Liquid Spring (Includes TM-21 A/C Con |                    |
|   | Chevy 5500, 169 wb, 4x4 w/Liquid Spring (Includes TM-21 A/C Col  |                    |
|   | CHEVROLET TYPE I 2024 CO   | NVERSION ONLY      |
|   | Chevy 2168 Super Warrior (172" body, front mount condenser, cab step   | s included)        |
|   |  |                    |
|   | Freightliner / International TYPE I - 20   | 24 CONVERSION ONLY |
|   |  |                    |
|   | 2168/Freightliner / International Med-Duty   |                    |
| _ |  |                    |
|   |  |                    |

|          |  | MODULE  |
|----------|--|---|
|          | •Warrior: 148"L x 68" Headroom                                     | • All Body Openings "Seamless"                                  |
| <u> </u> | <ul> <li>Super Warrior: 168"L x 72" Headroom</li> </ul>            | All Door Latches Mounted Behind Gaskets                         |
|          | <ul> <li>Aluminum Diamond Plate Running Boards</li> </ul>          | <ul> <li>Exterior Compartment @ Front Left for</li> </ul>       |
|          | Rear Mud Flaps   | Storage of Oxygen Tank and Back Boards                          |
|          | <ul> <li>Totally "Seamless" Body Construction</li> </ul>           | <ul> <li>Exterior Compartment Adjustable Shelving</li> </ul>    |
|          | <ul> <li>Exterior Side &amp; Roof Panels .125" Aluminum</li> </ul> | Exterior Compartment Lighting                                   |
|          | One-Piece Exterior Side Panels                                     | Cast "Grabber" Door Holders                                     |
|          | One-Piece Crowned Roof   | <ul> <li>Lower Body Impact Rub Rails</li> </ul>                 |
|          | <ul> <li>Frame Members 2" x 2" Aluminum Tubing</li> </ul>          | Polished Stainless Steel Fenderettes                            |
|          | <ul> <li>Frame Members on 12" Centers or Less</li> </ul>           | Flip-up Rear Step Bumper w/                                     |
|          | Diamond Plate Shields:   | 4" x 18" Dock Bumpers   |
|          | - Across Lower Rear of Body  |   |
|          | - Across Lower Front of Body                                       |   |
|          | - Lower 1/3 of Entry Doors   |   |
|          | All Exterior Doors "Pan-Formed" / Extruded                         |   |
|          | Double Break Construction  |   |
|          | 4  |   |
|          |  |   |
|          | Į  | WARNING SYSTEM  |
|          | <ul> <li>Two Red Whelen ION-T Mounted in grill</li> </ul>          | • Two LED Whelen 9x7 Rear Load Lights                           |
|          | • Four Red Whelen ION-T Intersection Lights                        | • Primary / Secondary Switching                                 |
|          | Mounted in Front and Rear Fenders                                  | Whelen 295 SLSA1 Siren  |
|          | <ul> <li>Eight Red LED Whelen 9x7 Modular Lights</li> </ul>        | • Siren / Horn Switch   |
|          | One Clear LED Whelen 9x7 Front                                     | Cast Siren Speaker  |
|          | Modular Light  | Rear DOT Lighting Whelen LED 4x6 w/                             |
|          | One Amber LED Whelen 9x7 Rear                                      | Chrome Flanges: Red Tail / Brake,                               |
|          | - Modular Light  | Amber Arrow Turn  |
|          | <ul> <li>Two LED Whelen 9x7 Scene Lights Per Side</li> </ul>       | • Reverse are LED   |
|          |  |   |
| ·        |  |   |
|          |  | PAINT & MARKINGS  |
|          |  |   |
|          | • 8" Belt Line Paint Stripe  | • "No Smoking" & "Fasten Seat Belt" Signs                       |
|          | Base Coat / Clear Coat Modular Paint                               | Ambulance / Star-of-Life Decals                                 |
|          | 4  |   |
|          |  |   |
|          |  | ELECTRICAL  |
|          | <ul> <li>Digital Voltmeter</li> </ul>                              | Battery Switch Activated via Ignition Switch                    |
|          | Audible Low-Voltage Alarm  | Open Door Warning Light   |
|          | Weldon V-Mux Electrical System w/ Load                             | Hand Held 300,000 CP Spotlight                                  |
|          | Management & Sequencing System                                     | Whelen Dual Intensity LED Patient                               |
|          | <ul> <li>Wiring Color-Coded and Heat Embossed</li> </ul>           | Compartment Dome Lights   |
|          | Every 6" w/ Function   | Exterior Weatherproof Shoreline Receptacle                      |
|          | Power Distribution Panel Easily Accessible                         | Two Interior 110V Duplex Receptacles                            |
|          | Via Hinged Access Door in Action Area                              | Two Interior 12V Cigar Style Receptacles                        |
|          | <ul> <li>One Piece Molded Front Switch Console</li> </ul>          | One Pre-Wire Antenna Cable                                      |
|          | <ul> <li>Hinge Mounted Attendant Switch Console</li> </ul>         | Electrical Back-up Alarm  |
|          | <ul> <li>Control Console Backlighting Dimmer</li> </ul>            |   |
|          | -  |   |
|          | 1  | NITEDIOD  |
|          | ļ  | INTERIOR  |
|          | <ul> <li>All Vertical Corners 1" Radii</li> </ul>                  | • R-29 Reflectics Insulation Through-out Module                 |
|          | <ul> <li>Stainless Steel Aisle Panel, Left Side,</li> </ul>        | • Thermostatically Controlled Patient                           |
|          | _ Full Length x 18" x .060"  | Compartment Heat & Cool System                                  |
|          | <ul> <li>Lon-Plate, non skid Vinyl Flooring</li> </ul>             | • 3-Speed Manual Fan Control                                    |
|          | Rolled 3" Up Both Sides of the Aisle                               | Rear Heat & Cool Unit Mounted Floor Level;                      |
|          | EMT Seat, Pedestal Mounted Deluxe                                  | * Moisture Drains Directly Through Floor                        |
|          | Seamless Vinyl Captains Chair w/3-Pt Belt                          | * Short Coolant Circulation Distance                            |
|          | CPR Seat, three piece, molded contoured cushions                   | * Eliminates Vertical Circulation of Coolant                    |
|          | Squad Bench  | * Unit Easily Accessible for Maintenance                        |
|          | Retractable Seat Belts for All Locations                           | Overhead Air Distribution w/ Floor Level Filtered               |
|          | <ul> <li>Handicap Style, 1 ½" Diameter, Full Length,</li> </ul>    | Air Return for Optimum Circulation                              |
|          | - Stainless Steel Overhead Grab Rail. This Rail                    | • Two Recessed, Swing-up Dual IV Hangers                        |
|          | shall be treated with Agion Anti-Bacterial                         | <ul> <li>"Zico" Retaining Bracket for Oxygen "M" Cyl</li> </ul> |
|          | _ Coating.   | • Three "Ohio" Oxygen Outlets                                   |
| <u> </u> | • Handicap Style, 1 1/2" Diameter, Stainless Steel                 | SSCOR Suction System  |
|          | Door Pulls on Patient Compartment Doors.                           | Locking Sharps Container (Shipped Loose)                        |
|          | These Bars shall be treated with Agion Anti-                       | Locking Drug Compartment  |
|          | Bacterial Coating.   | Digital Clock   |
|          | Padded Bulk-Head Cabinet Doors                                     | Stryker "Performance Load" Cot Fastener                         |
|          | <ul> <li>ALS Compartment w/ In/Out Access</li> </ul>               | Seamless Seat Cushions  |
|          | -  |   |
|          |  |   |
|          |  |   |

|          | ·                                     |   |
|----------|---------------------------------------|---|
|          | · · · · · · · · · · · · · · · · · · · | EMERGENCY & EXTERIOR LIGHTING & SIREN OPTIONS                                 |
| Qty      |                                       | Warning & Intersection Lights, Wig-Wag  |
| 29       |                                       |   |
|          | W-01                                  | Chrome Flanges for 9 x 7 (per light)  |
|          | W-02                                  | Chrome Flanges for 7 x 3 or 6 x 4 Lights                                      |
|          | W-03                                  | Chrome Flanges for M9   |
|          | W-04                                  | Chrome Flanges for M6 or M7   |
|          | w-05                                  | Chrome Flanges for ION  |
| Qty      | · · · · · · · · · · · · · · · · · · · | Premption   |
| 20       |                                       |   |
|          |                                       | Opti-Com  |
|          | W-07                                  | Tomar Emitter   |
| 0        | · · · · · · · · · · · · · · · · · · · | Custom Linkthous  |
| Qty      | ·                                     | Custom Lightbars  |
|          | ·                                     |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
| -        |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
| Otv      | · ·                                   | Directional Sticks  |
| Qty      | · · · · · · · · · · · · · · · · · · · | Directional Sticks  |
|          | W-08                                  | Whelen TAZ86 6-Super LED Traffic Advisor                                      |
|          |                                       | Whelen TAL 85 LED 8 Light Traffic Advisor                                     |
|          |                                       |   |
| Qty      |                                       | LED Strip Lighting  |
|          |                                       |   |
|          |                                       |   |
| <u> </u> | W-10                                  | Whelen Strip-Lite, Red or Amber   |
|          | W-11<br>W-12                          | Whelen Strip-Lite, Blue or White<br>Red Innovative Strip Light, Dual Elements |
|          | W-12<br>W-13                          | Amber Innovative Strip Light, Single Element                                  |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |

|          |      | EMERGENCY & EXTERIOR LIGHTING & SIREN OPTIONS  |
|----------|------|--|
|          |      | Continued  |
| Qty      |      | Whelen Smart Linear LED's  |
| Qıy      |      |  |
|          | W-15 | Additional 900 Solid LED, R, B or A  |
|          |      | Additional 900 Solid LED, C  |
|          |      | Additional 900 Green<br>Additional 900 R/B or R/A LED  |
|          |      | Additional 900 R/C or B/C LED  |
|          | W-20 | Upgrade 900 LED to Solid C   |
|          |      | Upgrade 900 LED to Green   |
|          |      | Upgrade 900 to Split R/B or R/A  |
|          |      | Upgrade 900 to Split R/C or B/C<br>700 LED I.L.O. ION-T, R, B or A                               |
|          |      | 700 LED I.L.O. ION-T R/B or R/A  |
|          | W-26 | 700 LED I.L.O. ION-T, All or 1/2 Clr   |
|          |      | Additional 700 LED R, B or A   |
|          |      | Additional 700, R/B or R/A<br>Additional 700 LED All or 1/2 Clr                                  |
|          |      | Additional 600 LED, R, B or A  |
|          |      | Additional 600, R/B or R/A   |
|          |      | Additional 600 LED All or 1/2 Clr  |
| ┝──┼     |      | Additional 500 LED, R, B or A  |
| ┝──┼     |      | Additional 500, R/B or R/A<br>Additional 500 LED, All or 1/2 Clr                                 |
|          |      | Upgrade 900 to M9 LED, R, B, A, R/B, R/A   |
|          |      | Upgrade 900 to M9, All or 1/2 Clear  |
|          |      | Additional M9, Red, B, A, R/B, R/A   |
|          |      | Additional M9 (All or 1/2 CLR)   |
| ┝──┼     |      | Upgrade ION-T to M6 Red, B, A<br>Upgrade ION-T to M6, R/B, or R/A                                |
|          |      | Upgrade ION-T to M6, RID, of IVA   |
|          |      | Additional M6 LED, R, B or A   |
|          |      | Additional M6, R/B or R/A  |
| ┝──┼     |      | Additional M6 LED, All or 1/2 Clr  |
| ┝──┼     |      | Upgrade ION-T to M7 R, B or A<br>Upgrade ION-T to M7 R/B, or R/A                                 |
|          |      | Upgrade ION-T to M7 All or 1/2 CLR   |
|          |      | Additional M7 LED, R, B or A   |
|          |      | Additional M7 LED, R/B, R/A  |
| ┝──┼     |      | Additional M7 LED, All or 1/2 Clr  |
| ┝──┼     |      | Whelen ION-T, R, B, A<br>Whelen ION-T, R/B or R/A  |
|          |      | Wheten ION-T, All or 1/2 Clr   |
|          |      | Whelen OS Light  |
|          | W-56 | Add Any Light to Interior of Door (Add to Light Price)   |
|          |      |  |
| ┝──┼     |      | Specify Flash Pattern to set LED's to  |
|          |      | LED's to be: Unsynchronized Synchronized on K Flasher  |
| Qty      |      | Scene Lights   |
|          |      |  |
| $\vdash$ |      | Whelen 90COENZR 24-DIODE Scene Light, Additional   |
| ┝──┼     |      | Whelen 700 Scene LED Additional<br>M9 LED Scene, Upgrade   |
| ┝──┼     |      | M9 LED Scene, Additional   |
|          |      | M7 LED Scene, Upgrade  |
|          |      | M7 LED Scene, Additional   |
| ┝──┼     |      | Pioneer Single w/Flange, Upgrade PCPSM1C   |
| ┠──┼     |      | Pioneer Spot & Flood w/Flange, Upgrade PCPSM2C   |
| ┠──┼     |      | Pioneer Single w/Flange, Additional PCPSM1C<br>Pioneer Spot & Flood w/Flange, Additional PCPSM2C |
|          |      | Upgrade Brake/Tail to M6 (Pair)  |
| <b></b>  |      | Upgrade Turn to M6 (Pair)  |
|          |      | Upgrade Reverse to M6 (Pair)   |

|     |      | EMERGENCY & EXTERIOR LIGHTING & SIREN OPTIONS   |
|-----|------|---|
|     |      | Continued   |
| Qty |      | Siren & Speakers  |
|     | W-70 | Federal Rumbler (Only Available w/ Federal Siren, Whelen 295 Sirens, Signal #SS700-008, Code 3 VCON & 3997RS, Carson SC-4074 Commander) |
|     | W-71 | Federal E-Q2B   |
|     | W-72 | Federal PA-300  |
|     | W-73 | SA-400-17 w/Mechanical Tone   |
|     |      | SA-430 Siren w/ Remote Control Head, Upgrade  |
|     |      | SA-441 Siren w/Remote Control Head, Upgrade   |
|     |      | SA-441-17F w/Mechanical Tone  |
|     |      | 295 HFSC9 Dual Tone   |
|     |      | 295 HFS2 Remote Head  |
|     |      | 295 HFS7 Remote Head, Dual Amps   |
|     |      | Whelen Howler (Only Available w/ Whelen Siren)  |
|     |      | Buell Dual Air Horns Mounted Under Front Bumper   |
|     |      |   |
|     | W-82 | Buell #16122 Compressor & # 5440 2nd Tank Upgrade   |
| Qty |      | Exterior Lighting   |
|     |      |   |
|     | W-83 | 6 x 4 LED Turn Lights w/ Chrome Flanges Mounted Front of Module, (Per Pair)   |
|     | W-84 | M6 Turn Lights w/Chrome Flanges on Front of Mod (per pair)  |
|     | W-85 | Hella Fog Lights  |
|     | W-86 | PIAA LED Fog Lights   |
|     |      | LED Running Board Lights  |
|     |      | Zico LED Under Body Lights (Per Pair)   |
|     |      | Zico Angled Reverse Lights White (Per Pair)   |
|     |      | Zico Angled Reverse Lights Ville (Cer Pair)   |
|     |      | Additional LED Compartment Light to LED   |
|     |      | Techniques E-41 LED Strip Lighting in all Compartments  |
| Qty |      | Additional Emergency & Exterior Lighting & Siren Options & Special Instructions   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |
|     |      |   |

|                                |      | ELECTRICAL OPTIONS   |
|--------------------------------|------|--|
|                                |      |  |
| Qty                            |      | Inverters, Chargers, Batteries, Shorelines & Outlets   |
|                                | E 01 | Pre-Wire for Vanner Inverter with Remote Switch  |
|                                |      | Vanner Inverter / Conditioner w/ Remote Switch, Model LSC12-1100   |
|                                | E 02 | Choose One: Inverter on with Ignition Switch in Rear Panel   |
|                                |      |  |
|                                |      | Iota P.C. 30 Battery Charger   |
|                                | E-04 | Iota P.C. 45 Battery Charger (Requires 30 Amp Shoreline)   |
|                                |      | NOTE: BATTERY CHARGER REQUIRED IN KKK-F  |
|                                |      | NOTE: DATTERT CHARGER REQUIRED IN RRR-T  |
|                                |      | Add 2nd 20amp shoreline and circuit  |
|                                |      | OEM Batteries Mounted in Slide Out Tray in Exterior Battery Compt. (N/A on Type I)                               |
|                                |      | Additional (3rd) Matching Battery (Requires Ordering Exterior Battery Compartment                                |
|                                |      | Upgrade to Twist Lock 30 Amp Shoreline<br>Upgrade to Kussmaul Auto Eject Shoreline Plug, 20 Amp                  |
|                                |      | Upgrade to Kussmaul Auto Eject Shoreline Plug, 20 Amp  |
|                                |      | Shoreline Indicator at Shoreline   |
|                                |      |  |
| Qty                            |      | Outlets & Interior Lighting  |
|                                |      |  |
|                                | E-12 | 110 V Outlet, Additional per Outlet  |
|                                | F-13 | 12V DC Outlet, Cigar Style, Additional per Outlet Note: Outlets will be Ignition Hot unless otherwise specified  |
|                                |      | 110/USB Outlet   |
|                                |      | Dual USB Outlet  |
|                                |      | Single Overhead Reading Light in Cab   |
|                                |      | R/W Dome Light in Cab  |
|                                |      | LED Federal Little Lite<br>Check-Out Lights, 2 - 12 Volt LED, 36",   |
|                                |      | Additional LED Check Out Lights (Per Light)  |
|                                |      | Interior Cabinet Lighting w/On/Off Switch Mounted in Action Panel (Strip LED)                                    |
|                                | E-22 | Power Door Lock Control Head   |
|                                |      | Power Door Lock Per Door   |
|                                |      | LED Lights (3) Above Rear Entry Doors (Brake & Turn)   |
|                                |      | Whelen Round LED Domelights w/Chrome Flange (Upgrade per Lt)<br>Whelen Rectangular LED Domes (Upgrade per Light) |
|                                |      | Intertech Round LED Domes (Upgrade per Light)  |
|                                |      | Additional Dome Lights (Add to Cost of Upgrade Light, if Ordered )   |
|                                | E-29 | Upgrade Dome to Red/Clear  |
|                                |      | Upgrade Dome to Blue/Clear   |
|                                | E-31 | Heart of Chrome Customs UV Light   |
| Qty                            |      | Switches & Secure Idle   |
| Įιy                            |      | Switches & Secure fuit   |
|                                | E-32 | (3) Switch Auxiliary Panel   |
|                                | E-33 | Extra Switch & Pre-Wire (Separate From V-MUX System)   |
|                                |      | Hidden Switch in Grill for Door Locks  |
|                                |      | Idle Lock Security System  |
|                                | E-36 | 2nd Switch Panel on Curbside Wall  |
| Qty                            |      | Pre-wires, Radios, Intercom, & Clocks  |
| <b>C</b> <sup>1</sup> <i>J</i> |      |  |
|                                | E-37 | Antenna Pre-Wire, (additional per Pre-Wire)  |
|                                | E-38 | Pre-Wire & Ground for Radio, (additional per Pre-Wire)   |
|                                | E 20 | Install Customer Radio Cable (each)  |
|                                |      | Note: Specify Brand of Radio Cable:  |
|                                |      | Install Customer Radio Head (each)   |
|                                |      | Two Radio Speakers in Patient Compartment  |
|                                |      | Volume Control for Rear Speakers Mounted in Action Area  |
|                                |      | Intelli-Tech Time Manager  |
|                                | E-45 | Carbon Monoxide Monitor  |
|                                |      |  |
|                                |      |  |
|                                |      |  |

| Qty       |      | ELECTRICAL OPTIONS   |
|-----------|------|--|
|           |      | Continued  |
|           |      |  |
|           |      |  |
| Qty       |      | V-Mux Options  |
|           |      |  |
|           |      |  |
|           |      | Warning Lights in Secondary w/Park Brake or Park ("Park" n.a. on some chassis')                                |
|           |      | Park Brake Override Switch   |
|           |      | Full Set of Diagnostic Screens (w/Vista IV Upgrade Only)   |
|           |      | Truck Information Screen (w/Vista IV Upgrade Only)   |
|           |      | Up to 10 Intensities on Dome Lights (Off-Hi-Lo is Standard)  |
| <u> </u>  |      | Up to 10 Speeds on Exhaust Fans (Off-On is Standard)<br>Up to 10 Speeds on HVAC Fan                            |
|           |      | Custom Flash Patterns (Specify on Page 9)  |
|           |      | Rear Flashers on in Reverse (Specify on Page 9)  |
|           |      | Side Scene on in Reverse   |
|           |      | Brake Override   |
|           |      | Custom Load Sequencing (On or Off) (Specify on Page 9)   |
|           |      | Custom Load Shedding (Specify on Page 9)   |
|           |      | Upgrade Switches to Vista IV Screens   |
|           |      | 3rd Vista IV Monitor in Rear   |
|           |      | 3-Switch Pod & 3-Lights for Silent Intercom  |
|           |      | Reverse Camera Tied into V-MVX Screen (w/Vista IV Upgrade Only)  |
| $\square$ |      | O2 Sensor for V-MVX System (Requires Ordering M-16) (w/Vista IV Upgrade Only)                                  |
|           |      | Exterior Temperature Readout (w/Vista IV Upgrade Only)   |
|           | E-65 | Ammeter Readout (w/Vista IV Upgrade Only)  |
|           |      |  |
| Qty       |      | HVAC Systems   |
|           |      |  |
|           |      | 110V Heater in Patient Compartment w/ 2nd Shoreline  |
|           |      | Danhardt 110V Heat/Cool Unit Installed in Squad Bench  |
|           |      | Stadco Model CP7 Diesel 6KW Liquid Cooled Generator (S-Warrior Only)   |
| <u> </u>  |      | Norcold 1.7 cubic feet Refrigerator Dometic Refreigerated Drawer CD-030  |
|           |      | IV Warmer Pad, (Pet Pad) (110V)  |
|           |      | IV Warner Pad, (Smithworks) (12V)  |
|           |      | Digital Thermostat   |
|           |      | Auxiliary Condenser  |
|           |      | Upcharge to Install Condensor on Front of Module   |
|           |      | Rooftop-Mount Condenser  |
|           | E-77 | 2nd Engine - Driven Compressor   |
|           |      |  |
|           |      |  |
| Qty       |      | Mirrors, Hind-Sight, Backup Camera, & Spotlights   |
|           |      |  |
|           |      | Velvac XG2020 Velvac Heat/Remotes, Black White (Black Std. on G-Cuts)  |
|           | E-79 |  |
|           |      | Brigade Sonar Backup Assist  |
|           |      | Safety Vision Color Reverse Camera   |
|           |      | Safety Vision Color Reverse & Interior Cameras   |
|           |      | Brigade Color Reverse Camera   |
|           |      | Brigade Color Reverse and Interior Cameras<br>Go-Light Wireless Remote Control Roof Mount LED Spotlight, White |
|           |      | Go-Light Wireless Remote Control Roof Mount LED Spotlight, White   |
| $\vdash$  | E-00 | Go-Light whereas Remote Control Root Mount LED Sponight, Chiolite  |
| ┝──┼─     |      |  |
|           |      |  |
|           |      |  |
|           |      |  |
|           |      |  |
|           |      |  |
|           |      |  |
| · · ·     |      |  |
|           |      |  |

| Qty      | ELECTRICAL OPTIONS                                  |  |  |  |
|----------|---|--|--|--|
|          | Continued   |  |  |  |
|          | DEDUCTIONS  |  |  |  |
|          | DEDUCTIONS:       E-87     Delete: (2) Dome Lights  |  |  |  |
|          |   |  |  |  |
| Qty      | Additional Electrical Options & Special Instruction |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
| <u> </u> |   |  |  |  |
| <u> </u> |   |  |  |  |
|          |   |  |  |  |
| <u> </u> |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |
| <u> </u> |   |  |  |  |
|          |   |  |  |  |
|          |   |  |  |  |

|             |      | MEDICAL OPTIONS  |
|-------------|------|--|
| Qty         |      | I.V. & Suction   |
|             | M-01 | Perko I.V. Clip with Velcro Strap  |
|             |      | Recessed Swing-Up Dual I.V. Hanger   |
|             | M-03 | I.V. Pole By Action Rear   |
|             | M-04 | Sscor VX-2 Portable / Permanent Suction I.L.O. Standard  |
| Qty         |      | Cot Mounts   |
|             |      |  |
|             |      | Ferno Stat-Track I.L.O. Performance Load   |
|             |      | Ferno Stat-Track w/ICS   |
|             |      | Ferno Inline Cot Mount<br>Ferno Pro F1 Cot Mount w/ICS   |
|             |      | Stryker Performance Load Cot Mount with Inductive Charging   |
|             |      | Stryker Universal Floor Plate Only   |
|             |      | Stryker Power Load I.L.O. Performance Load   |
|             |      | Install Customer-supplied Power Load   |
|             |      | Install Floor Plate for Mass-Casualty Hook (Does not include Hook)   |
|             |      | Install Mass-Casualty Floor Plate & Hook (Does not include Front Antler needed with performance load)<br>Front Antler for Performance Load Mass-Casualty |
| <u> </u>    |      | Delete Standard Stryker Performance-Load (Demo Order Only)   |
| <del></del> |      | Provide Model Number of Customer's Stretcher   |
|             |      |  |
| Qty         |      | Oxygen   |
|             |      |  |
|             |      | Additional O2 Outlet Over Squad Bench<br>O2 Regulator for "M" Tank   |
|             |      | O2 Flow Meter /Tube-Type   |
|             |      | O2 Flow Meter / Dial-Type Flowmeter  |
|             | M-21 | Electric O2 Solenoid w/Switch  |
|             |      | Amico Digital O2 Gauge w/Regulator   |
|             | M-23 | 2nd "M" Tank Bracket   |
|             | M-24 | Zico Hydraulic O2 Bracket (Specify M or H Cylinder) (Note:Requires M-21 & M-22)<br><b>This Option Eliminates the O2 Pass-Through</b>                     |
|             |      | Zico Portable O2 Bracket QRD2  |
|             |      |  |
|             |      |  |
|             |      | SELECT STANDARD D or JUMBO D   |
| Qty         |      | Additional Medical Options & Special Instructions  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |
|             |      |  |

|             |              | INTERIOR OPTIONS  |
|-------------|--------------|---|
|             |              |   |
| Qty         |              | Laminate & Vinyl  |
|             |              |   |
|             | I-01         | Custom Laminate Color   |
|             | I-02         | Custom Vinyl Color  |
|             |              |   |
|             |              | Note Provide Colors:  |
|             |              | Laminate Color:   |
|             |              | (Standard Colors: Dove Grey, Grey Glace, Grey Nebula)                                   |
|             |              | Vinyl Color:  |
|             |              | (Standard Colors: Cobalt Blue, Wedge Wood Blue, Ash Gray,<br>Desert Rose Red)           |
|             |              | Lonplate Color:   |
|             |              | #176 Pewter, #424 Gunmetal, #165 Sapphire   |
|             |              | #1/01eweer, #424 Guinicear, #105 Sappline   |
| Qty         |              | Flooring, Aisle, Backboard Slots  |
| <b>C</b> -7 |              | <b>b</b> , |
|             | I-03         | Lonspeck #SX112 Magnetic Gray   |
|             |              | Lon-Coin Flooring Note: Provide Color:  |
|             | I-04         |   |
| I T         |              | Lon-Plate Flooring, Custom Color Note: Provide Custom                                   |
| $\vdash$    | I-05         |   |
|             | I-06         | Composite Subfloor  |
|             |              |   |
| 0           |              |   |
| Qty         |              | Seating, Squad Bench, EMT, CPR  |
|             | 1.07         | Curring Dedented for EVC Attendent Sect   |
|             | I-07         | Swivel Pedestal for EVS Attendant Seat Price to Upgrade EMT Seat:                       |
|             | 1.08         | 3-Pt. Child Seat  |
|             |              | 4-Pt. Bucket Seat   |
|             |              | 4-Pt. Child Seat  |
|             |              | 5-Pt. Bucket Seat   |
|             |              | 5-Pt. Child Seat  |
|             |              | 6-Pt. Bucket Seat   |
|             |              | 6-Pt. Child Seat  |
|             |              | Add Recline to EVS Seat   |
|             | I-16         | EVS Mobility I w/3-pt, 1769 Seat NOTE: This Seat Requires 39" From Wall for Swivel      |
|             | I-17         | 3-Pt 1769 Seat, fixed Pedistal, I.L.O. Bench or CPR                                     |
|             | I-18         | 4-Pt 1769 Seat, fixed Pedistal, I.L.O. Bench or CPR                                     |
|             | I-19         | Armrest for EVS Seat (Each)   |
|             |              | 6-Point Seat Belt, Per Position   |
|             |              | Note: Specify Color (If no color is chosen, black will be provided:                     |
|             |              | Black Orange Red Yellow   |
|             | I-21         | Aluminum Plates in Wall for Future Installation of 6-Pt. Belts (per seating position)   |
|             | I-22         | Cargo Net, End of Squad Bench   |
| ┝──┤        |              | 12" Seat Belt Extension   |
| ┢──┤        | I-24<br>I-25 | Seat Belt Monitor (requires sensors below)<br>Sensor for EVS Seat (per position)        |
| <u> </u>    | I-25<br>I-26 | Sensor for 2-Point Belt (per position)  |
| ┝──┼        | I-20<br>I-27 | Sensor for 6-Point Belt (per position)  |
|             | 1-2/         |   |
|             |              |   |
|             |              |   |
|             |              |   |
|             |              |   |
|             |              |   |
|             |              |   |
| $\vdash$    |              |   |
| ┝──┤        |              |   |
|             |              |   |
| ┝──┤        |              |   |
| ┝──┤        |              |   |
| ┝──┼        |              |   |
| ┝──┼        |              |   |
| ┝──┤        |              |   |
| ┝──┤        |              |   |
| ┣──┤        |              |   |
|             |              |   |

|          | ]                                     | INTERIOR OPTIONS  |
|----------|---------------------------------------|---|
|          |                                       | Continued   |
| Otv      |                                       | Cabinetry, Windows, Marker Boards, Shelves, & HVAC Ducts  |
| Qty      | · · · · · · · · · · · · · · · · · · · | Cabinetry, windows, Marker Boards, Sherves, & HVAC Bucts  |
|          |                                       | Note: Select One of the Following No/Charge Front Console Configurations:                         |
|          |                                       | Dual Drink Holders  |
|          |                                       | Driver's Side Drink Holder Only<br>No Drink Holders will be provided (unless otherwise noted)     |
|          | I-28                                  | Radio/Notebook Cabinet in Cab (Standard Design) (Standard in T-I's)                               |
|          | I-29                                  | Radio/Notebook Cabinet in Cab (Design Required)   |
|          | I-30                                  | Customize Console in Type I   |
|          | I-31<br>I-32                          | Removable Padded Armrests for Console (Pair)<br>Aluminum Cabinetry (Requires Spray Coating)       |
|          |                                       | Choose Zolatone Color:  |
|          |                                       | NOTE: Depending on Cabinet Layout, Varying Amounts of Wood Panels will be used in Construction    |
|          | I-33                                  | Narrow Bulkhead   |
|          | I-34                                  | Cabinet Over Rear Doors   |
|          | I-35                                  | Cabinet Over Squad Bench, (Requires 43" Between Bench Cushion & Cabinet) (Standard in 2168)       |
|          |                                       | Cabinet over CPR Seat (Requires 43" between Bench Cushion & Cabinet) (Std. in 2168)               |
|          | I-36<br>I-37                          | On 72" Headroom Units, Drop Bench and CPR Seat 2" Adding 2" to Overhead Cabinets                  |
|          | I-37<br>I-38                          | (WILL ELIMINATE SHARPS & WASTE, AND 02 RECESSED IN BENCH )  |
|          | I-39                                  | Cabinet @ Head of Squad Bench for Portable O2, (Brackets Not Included)                            |
|          | I-40                                  | Cabinet @ Head of Squad Bench for Portable O2, Recessed Below Floor Level (Brackets Not Included) |
|          | I-41                                  | Angled Cabinets Forward and AFT of CPR Seat   |
|          | I-42                                  | Tinted Plexiglas in Cabinet Windows   |
|          |                                       | Re-stocking Seals in Cabinet Windows<br>Tilt-up Speed Load Cabinet Windows, w/latch (per window)  |
|          |                                       | Interior Access to Exterior Compartment   |
|          | I-46                                  | Window Over Squad Bench; 16 x 32 w/Slide - Passenger Side   |
|          | I-47                                  | Window Over Squad Bench; 16 x 32 w/Slide - Driver Side  |
|          |                                       | Sliding Privacy Panel w/Dry Marker Board<br>Telescoping Marker Board                              |
|          |                                       | Solid Mounted Dry Marker Board  |
|          |                                       | Track-Type Adjustable Shelves in Interior Cabinets, (per shelf)                                   |
| <u> </u> | I-52<br>I-53                          | Fixed Shelf<br>Fixed Divider  |
|          |                                       | Adjustable Divider Track  |
|          |                                       | Adjustable Divider (Requires above track)   |
|          |                                       | Additional Adjustable Shelf & Light in ALS  |
|          |                                       | Monitor Shelf to the Rear of the CPR Seat<br>Ceiling HVAC Duct                                    |
|          |                                       | Glove Storage Over Side Entry Door  |
|          |                                       | Two (2) Glove Storage Units Over Rear Doors   |
|          |                                       | Two (2) Glove Storage Recessed Into Rear Entry Doors  |
|          | I-62<br>I-63                          | Recessed Suction in Left Aisle Wall (No Door) Door For Above                                      |
|          | I-03<br>I-64                          | Chevrons on Entry Door Kickplates (Per Door)  |
|          |                                       | Color of Chevrons:  |
|          |                                       | NOTE: Requires EX-35  |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |
|          |                                       |   |

|                  |              | INTERIOR OPTIONS  |
|------------------|--------------|---|
|                  |              | Continued   |
|                  |              |   |
| Qty              |              | Doors, Locks, & Latches   |
|                  |              |   |
|                  | I-65         | Café Double Doors, (Warrior)  |
|                  | I-66         | Full Plexiglas ALS Doors (3/8" Plexiglas, No Frames)  |
|                  | I-67<br>I-68 | Single Roll-up Shutter on ALS<br>Lock for Roll-up Shutter on ALS  |
|                  | I-68<br>I-69 | Lock on Interior Cabinet  |
|                  | I-02<br>I-70 | Simplex Combination Lock  |
|                  | I-71         | Southco Stainless Steel Latches, (per Latch)  |
|                  | I-72         | Southco Stainless Steel D-Ring Latch (per latch)  |
|                  | I-73         | Chrome Rectangular Latch (per latch)  |
|                  |              |   |
| Qty              |              | Counter Tops  |
|                  |              | Note: Select One of the Following No/Charge Standard Counter Top Colors:  |
|                  |              | Speckled Gray   |
|                  |              | Speckled Blue   |
|                  |              | Speckled Red  |
|                  |              | Speckled Tan  |
|                  |              | Speckled Color Finish in Silk Stone Action Area Countertop  |
|                  | I-75         | Speckled Color Finish in Silk Stone Monitor Shelf Countertop  |
|                  | 1.72         | Note: Provide Color of Silk Stone Counter Top if Ordered:   |
|                  | I-76         | Custom Silkstone Color  |
| $\left  \right $ | I-77<br>I-78 | Swivel Bracket for Zoll X Series Swivel Bracket for LP12 or LP15  |
|                  | I-78<br>I-79 | Swivel Bracket for LP12 or LP15<br>Technimount for 20LL X Series  |
|                  | I-79<br>I-80 | Technimount for LP15  |
|                  | 1-00         |   |
| Qty              |              | Sharps, Waste, & Drawers  |
|                  |              |   |
|                  | I-81         | Sharps & Waste Drawer   |
|                  | I-82         | Tilt-Out Sharps or Waste  |
|                  | I-83         | Sharps/Waste thru Fiberglass Counter into #2 Compartment (Warrior Only)   |
|                  | I-84         | Waste Disposal thru Silk Stone Countertop into #2 Outside Compartment   |
|                  | I-85<br>I-86 | Sharps Disposal thru Silk Stone Countertop into #2 Outside Compartment Drawer for General Storage (Indicate Location)   |
|                  | I-80<br>I-87 | Drawer with Flip-up Writing Service   |
|                  | I-87         | Sharps & Waste in Bench w/ Flip-Up Plexiglass Lids  |
|                  |              |   |
| Qty              |              | Grab Rails & Bars, Armrests   |
|                  |              |   |
|                  |              | Additional Grab Rail Over Squad Bench   |
|                  | 1-90         | Armrest/Bar at Head of Squad Bench, SS Removable<br>A-Bar w/Sharps & Waste @ Head of Squad Bench, SS Removable (Warrior Models Only) This Bar shall be treated with Agion |
|                  | I-91         | A-Bar W/Sharps & Waste @ Head of Squad Bench, SS Removable (warrior Models Only) This Bar shall be treated with Agion<br>Anit-Bacterial Coating                           |
|                  | I-91<br>I-92 | Custom A-Bar  |
|                  | I-92<br>I-93 | Armrest at Head of Squad Bench, Upholstered   |
|                  | I-94         | 12" Stainless Grab Handle   |
|                  | I-95         | Make Grab Bar Yellow (Price Each)   |
|                  |              |   |
|                  |              |   |
| Qty              | [            | Insulation & Sound Deadening  |
|                  | LOC          | Sound Deadening Under Floor   |
|                  | I-96<br>I-97 | 3M Sound Deadening on Back of Exterior Compartments   |
|                  | I-97<br>I-98 | Delux Insulation on Side Entry Step   |
|                  | 1,0          |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |
|                  |              |   |

|             |       | INTERIOR OPTIONS<br>Continued  |
|-------------|-------|--|
|             |       | Continued  |
| Qty         |       | Additional Headroom, Crawl Through (Type I), Bariatric Package       |
|             |       |  |
|             | I-99  | Custom Headroom. Fill in Height                                      |
|             | I-100 | Crawl Through to Cab, (Type I)                                       |
|             | I-101 | Move Struts to Ends of Bench<br>Move Paddle Latches to Ends of Bench |
|             | 1-102 | Nove Paddle Latches to Ends of Bench                                 |
|             |       | DEDUCTIONS:  |
|             | I-103 | Single Bench Lid   |
|             | I-104 | Delete Gas Struts on Bench   |
|             | I-105 | Laminated Counter  |
| Otv         |       | Additional Interior Options & Special Instructions                   |
| Qty         |       |  |
|             |       |  |
|             |       |  |
| $ \square $ |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
| $\square$   |       |  |
|             |       |  |
| $\vdash$    |       |  |
| $\vdash$    |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |
|             |       |  |

|            |              | EXTERIOR OPTIONS   |
|------------|--------------|--|
| Qty        |              | Custom Body Size, Compartments, Doors & Door Window  |
|            | EX-01        | Custom body Length. Fill in Length   |
|            |              | Please specify if you want #4 and/or #5 Widened at No Charge   |
|            |              | 4" Additional Cab Recess   |
|            |              | Additional Exterior Compartment, (per compartment)<br>Compartment Over Wheel Well w/ Rollout Drawer  |
|            |              | Change Exterior Compartment Size   |
|            |              | Side Entry Door Forward Layout   |
|            | EX-07        | Shallow-Depth or Staggered-Depth Compartment   |
|            | -            | Deepen #5 2" into Aisle (NOTE: Only 1 1/2" Available on  |
|            |              | Sprinter for 17 3/4" I.D. Depth.)<br>Double Door on Exterior Compartment ILO Single Door   |
|            |              | Recessed Pocket in Exterior Compartment ILO Single Door  |
|            |              | Sliding Windows in Rear Entry Doors (per pair)   |
|            |              | Lower Window in Entry Doors (each)   |
|            |              | Scorpion Lining in Exterior Compartment (Price Per Compartment)  |
|            |              | Scorpion Shelf   |
|            |              | Scorpion Divider Dry Deck All Compartments   |
|            |              | Dry Deck All Compartments<br>Stairchair Bracket  |
|            |              | Stairchair Bracket on Compartment Door   |
|            |              |  |
| Qty        |              | Shelves & Dividers   |
|            | <b>EX</b> 10 |  |
|            |              | Adjustable Shelving Unit in Exterior Compartment w/One Shelf up tp 12" wide<br>Adjustable Shelving Unit in Exterior Compartment w/One Shelf 12"-30" wide |
|            |              | Adjustable Shelving Unit in Exterior Compartment w/One Shelf 30"-48" wide  |
|            |              | Additional Shelf in Exterior Compartment up to 12" wide  |
|            |              | Additional Shelf in Exterior Compartment 12"-30" wide  |
|            | EX-24        | Additional Shelf in Exterior Compartment 30"-48" wide  |
|            |              | Aluminum Backboard Divider   |
|            |              | Adjustable Backboard Divider   |
|            |              | Roll-Out Tray in Comp.<br>Additional Backboard Strap   |
|            |              | Roll-Out Tray w/ Stair Chair bracket   |
| Qty        |              | Rear Bumpers & Entry Steps   |
|            |              |  |
|            |              | Fixed Rear Step Bumper   |
|            |              | Zico Retractable Side Entry Step   |
|            |              | Zico Manual Step   |
|            |              | Recessed Side Entry Step-Well w/ Remove Able Grip-Strut<br>Stainless Kick Plates on Entry Doors (three)  |
|            |              | Smooth Aluminum Kickplates (3)   |
|            |              | Dual Interior Emergency Door-Open Handles, Price per Door  |
|            |              | Additional Paddle on Dummy Door  |
|            |              | Nylon Retention Strap on Exterior Door   |
|            |              | Drop Skirt Line 4" from Right Rear Wheel to Right Front Corner, Add 2nd Entry Step<br>Painted Number Placards  |
| $\vdash$   | EX-40        |  |
|            |              |  |
|            |              |  |
|            |              |  |
|            |              |  |
| $ \vdash $ |              |  |
|            |              |  |
|            |              |  |
|            |              |  |
|            |              |  |
|            |              |  |
|            |              |  |
| └───┤      |              |  |
|            |              |  |
|            |              |  |
|            |              |  |

|                     |                                  | EXTERIOR OPTIONS   |
|---------------------|----------------------------------|--|
|                     |                                  | Continued  |
|                     |                                  |  |
| Qty                 |                                  | Rub Rail, Tow Hooks, Mud Flaps, Chains   |
|                     |                                  |  |
|                     |                                  |  |
|                     |                                  | Rear Tow Hooks (Mounted on Rear Bumper Frame)  |
|                     |                                  | Recessed Rear Tow Hooks  |
|                     |                                  | On-Spot Chains   |
| $ \longrightarrow $ |                                  | Grip Strut Running Boards, (vs. Diamond Plate) Available on RAM Only   |
|                     |                                  | Grip Strut Inserts in Running Boards   |
|                     |                                  | Reflective Tape in Rub RailFILL IN COLOR   |
|                     |                                  | Clear-View Star-of-Life (Per Window)<br>Stainless Steel Fuel Guard   |
|                     |                                  | 1pr. Rubber Mud Flaps for Front Wheels   |
| +                   |                                  | Taller Front Stone Guards  |
|                     |                                  | Southpark Handle at Side Door  |
|                     |                                  | Buckstop Bumper & Grill Guard, Black   |
|                     | EX-53                            | Buckstop Bumper & Grill Guard, Black (For Medium-Duty)   |
|                     |                                  | Buckstop Bumper Only, Black (For Medium-Duty)  |
| $\vdash$            |                                  | Ali Arc Bumper   |
| ┢───┼               |                                  | Thunderstruck Bumper   |
| ┢───┼               |                                  | Warn Transformer Black Grill Guard w/Center Bar  |
|                     |                                  | Luverne Black Prowler  |
| ┟──┼                |                                  | Luverne Stainless Prowler Grill Guard  |
|                     |                                  | Cast Fuel Fill Door<br>Rubber Fenderettes  |
| <b>├</b> ──┼        |                                  | Rubber Rub Rails   |
|                     |                                  | Billstein Shocks Per Axle  |
| +                   |                                  | DELETE:  |
|                     |                                  | Shelf in #2 Compartment  |
|                     |                                  | Exterior Compartment   |
|                     |                                  | Divider & Fixed Shelf in #1 or #5  |
|                     |                                  |  |
|                     |                                  |  |
| Qty                 |                                  | MISCELLANEOUS OPTIONS  |
|                     |                                  |  |
| $ \longrightarrow $ |                                  | Credit for Shipping Spare Tire Loose   |
|                     |                                  | Ford Jack & Tire Tools (not included in Cutaways)  |
| $ \longrightarrow $ |                                  |  |
|                     |                                  | Fire Extinguisher, 5lb   |
|                     | MS-04                            | Install Decals   |
|                     | MS-04                            |  |
|                     | MS-04                            | Install Decals   |
|                     | MS-04                            | Install Decals<br>Delete Decal Package   |
|                     | MS-04                            | Install Decals   |
|                     | MS-04<br>MS-05                   | Install Decals Delete Decal Package EXTENDED WARRANTIES  |
|                     | MS-04<br>MS-05<br>MS-06          | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000   |
|                     | MS-04<br>MS-05<br>MS-06          | Install Decals Delete Decal Package EXTENDED WARRANTIES  |
|                     | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000  |
|                     | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair?                              |
|                     | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000  |
|                     | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair?                              |
|                     | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair?                              |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
|                     | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
|                     | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |
| Qty                 | MS-04<br>MS-05<br>MS-06<br>MS-07 | Install Decals Delete Decal Package EXTENDED WARRANTIES Extended Electrical Warranty 7-years/100,000 Extended Cabinet Warranty 15-years/100,000 Note: Does Customer Require a Spot for Stryker Stair Chair? State Dimension and Location |

|     |      | EXTERIOR OPTIONS   |
|-----|------|--|
|     |      | (Continued)  |
|     |      |  |
| Qty |      | PAINT OPTIONS  |
|     | P-01 | Second Stripe at Skirtline to Match Beltline   |
|     |      | Hockey Stick Design, Single Stripe   |
|     |      | Heartbeat Stripe, (Osage Standard Design)<br>Custom Heartbeat to Match Customers Existing Unit             |
|     |      | 2nd Stripe, Same Color   |
|     |      | 2nd Stripe, Different Color  |
|     | P-07 | Paint Cab (Door jams included)   |
|     |      | <sup>1</sup> / <sub>2</sub> Red / <sup>1</sup> / <sub>2</sub> White Cab & Box (Including Door Jambs)       |
|     |      | Red Paint Color, (Additional Materials Cost)   |
|     |      | Yellow Paint Color (Add Material Cost)<br>Wet Sand & Buff  |
|     |      | Westsand & Buff roof   |
|     |      | Paint Roof White   |
|     | P-14 | Delete Standard Beltline Paint   |
|     | P-15 | Large SOL on Rear Quarter w/54" Ref. Snake   |
| -   |      |  |
| Qty |      | Pinstripe  |
|     | P-16 | 1/4" Reflective Pinstripe  |
|     |      | 1/2" Reflective Finstripe  |
|     |      | 7/8" Reflective Pinstripe  |
|     | P-19 | 2" & Wider Reflective Stripes, Per Inch of Width   |
|     |      | 6" 3M Reflective Chevron, One Color  |
|     |      | 6" 3M Reflective Chevron, Two Alternating Colors   |
|     |      | 6" Oracal Reflexite Chevron, One Color<br>6' Oracal Reflexite Chevron, Two Colors                          |
|     |      | 6" 3M Diamond Grade Chevron, One Color   |
|     |      | 6" 3M Diamond Grade Chevrons, Two Alternating Colors   |
|     |      | 6" Chevron on Rear Doors, One Color  |
|     |      | 6" Chevron on Rear Doors, Two Colors   |
|     |      | 6" Oracal Reflexite Chevron on Rear Doors, One Color   |
|     |      | 6" Oracal Reflexite Chevron on Rear Doors, Two Colors<br>6" Diamond Grade Chevron on Rear Doors, One Color |
|     |      | 6" Diamond Grade Chevron on Rear Doors, Two Colors   |
|     | 1.01 |  |
|     |      | NOTE: Chevrons outside & above Rear Doors  |
|     |      | Fill-in Color(s)   |
|     |      | NOTE: Pinstripe is One Stripe Above and One Below Standard Band  |
|     |      | TOTE. I insurpe is one surpe Above and one below standard band   |
|     |      | PROVIDE THE FOLLOWING IF APPLICABLE:   |
|     |      |  |
|     |      | Primary Paint Color<br>Primary Paint Code & MFG  |
|     |      | Secondary Paint Color  |
|     |      | Secondary Paint Code & MFG   |
|     |      | Primary Pinstripe Color  |
|     |      | Secondary Pinstripe Color  |
|     |      |  |
| Qty |      | Demo Decals  |
|     | P-32 | Osage Logo Decal   |
|     | P-33 | "Osage" Windshield Decall  |
| 0   |      |  |
| Qty |      | Additional Paint Options & Special Instructions  |
|     |      |  |
|     |      |  |
|     |      |  |
|     |      |  |
|     |      |  |
|     |      | 1  |

| Qty |   | Additional Options & Instructions |
|-----|---|-----------------------------------|
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     | - |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |
|     |   |                                   |

| <br>        | ORDER SUMMARY  |
|-------------|--|
|             | UKDEK SUMIMAKI   |
| <br>        |  |
|             |  |
|             |  |
|             |  |
|             |  |
|             |  |
|             |  |
|             | 5% Discount  |
|             | 5% Discount on Optional Items  |
|             |  |
|             |  |
|             |  |
|             |  |
|             |  |
|             | Osage believes the proposed design (identified above with an *) could increase the chance of injury to passengers, and recommends the following:   |
|             |  |
|             |  |
|             |  |
| <br>        |  |
|             |  |
| <br>        |  |
|             | There would be use additional part for this abanda   |
|             | There would be no additional cost for this change.   |
|             |  |
|             |  |
|             | The additional charge for this change would be   |
|             |  |
|             | Dealer directs that Osage modify the design as recommended.  |
|             | Dealer un etts tilat Osage inouny the design as recommended.   |
|             |  |
|             | Dealer acknowledges the above recommendation, and directs Osage to proceed with the original design.   |
|             |  |
|             | This recommendation was reviewed with the purchaser,   |
|             |  |
|             | of Date  |
|             |  |
|             | Endows Responsibility for Full Payment for Unit#   |
|             | within Three (3) Days of Completion.   |
| <br>        |  |
| <br>        |  |
|             | TERMS ARE F.O.B. LINN, MO  |
|             |  |
|             | OSAGE AMBULANCE WILL NOT BE RESPONSIBLE FOR THE  |
|             | PERFORMANCE OF CUSTOMER SUPPLIED OR SPECIFIED PRODUCT.   |
|             |  |
|             | THIS ORDER IS NOT BINDING UNTIL SIGNED BY BOTH AN OSAGE  |
| <br>        | DEALER, AND/ OR AN AUTHORIZED REPRESENTATIVE FOR AN OSAGE  |
|             | DEALER, AND AN AUTHORIZED REPRESENTATIVE FOR OSAGE   |
| <br>        | AMBULANCE.   |
|             |  |
|             |  |
| Signat      | ure of Osage Dealer or Authorized Agent Date Signed  |
| <u></u>     |  |
|             |  |
| <br>Signat  | ure of Authorized Representative of Osage Ambulance Date Signed  |
| <br>Digitat | a contraint the representative of confermination of the part of th |
|             |  |
| <br>        |  |
| <br>        |  |
|             |  |
|             |  |